

Displayline

<i>Caliper</i> <i>mm</i>	<i>Substance</i> <i>g/m²</i>	<i>Stiffness</i>	
		<i>Resonance method</i> <i>md</i>	<i>cd</i>
Screen / Screen			
1,25	925,00	810	415
1,50	1.050,00	1235	620
1,75	1.225,00	1725	870
2,00	1.275,00	2345	1235
2,25	1.425,00	3125	1690
2,50	1.575,00	4020	2090
Print / Print			
0,70	546,00		
0,80	625,00	240	135
0,90	700,00	340	195
1,00	775,00	445	270
1,10	850,00		
1,20	936,00		
1,25	1.000,00	1065	335
1,50	1.150,00	1635	530
1,75	1.275,00	2375	740
2,00	1.375,00	3175	1010
2,25	1.550,00	4310	1390
2,50	1.725,00	5645	1835
2,75	1.897,50		
3,00	2.070,00	5700	2885
Print / print (S)			
1,10	850,00	595	355
White Kraftliner white pe / kraftliner pe (S)			
1,20	880,00		
1,39	1.000,00		

White Kraftliner white pe / white kraftliner white pe (S)

1,26	900,00
1,61	1.150,00
1,68	1.200,00
1,75	1.250,00
1,80	1.300,00

CONCEPT

<i>Displayline</i>	<i>Specifications</i>	<i>Units</i>	<i>Tolerances</i>	<i>Test methods</i>
Caliper	see matrix	mm	±3 %	ISO 534
Substance	see matrix	g/m ²	±5 %	ISO 536
Stiffness	see matrix		±15 %	ISO 5629
Flatness	0	%	-0,3/+1,5 %	SKSB
Moisture content	8	%	±1,0 %	ISO 287