

Foodline

<i>Substance</i> <i>g/m²</i>	<i>Caliper</i> <i>mm</i>	<i>Stiffness</i>	
		<i>Resonance method</i> <i>md</i>	<i>cd</i>
Goldfoil / Silverfoil			
600	0,89	130	85
650	0,96	150	105
800	1,19	300	190
PET-liner Gold / woodfree white offset			
750	1,05	500	295
800	1,13	430	230
950			
900	1,27	650	355
950	1,32	730	400
1000	1,40	1060	640
PET-liner Silver / woodfree white offset			
750			
950			
1000			
Goldfoil / Goldfoil (S)			
600	0,98	130	85
750	1,09	250	160
Goldfoil / Silverfoil (S)			
600			
650			
700			
750			
800			
900			
Silverfoil / Silverfoil (S)			
700			

PET-liner gold / alu gold (S)

650

750

PET-liner gold / alu silver (S)

1050

CONCEPT

<i>Foodline</i>	<i>Specifications</i>	<i>Units</i>	<i>Tolerances</i>	<i>Test methods</i>
Substance	see matrix	g/m ²	±3 %	ISO 536
Caliper	see matrix	mm	±7%	ISO 534
Stiffness	see matrix	mNm	±15 %	ISO 5629
Flatness	0	%	-0,3/+1,5 %	SKSB
Pick up	< 10	%		ASCO 1969
Moisture content	7,5	%	±1,0 %	ISO 287